

## PRECISION DEMOUNTABLE CELLS

<u>Item #</u>	<u>Item Name</u>	<u>List Price</u>
<a href="#"><u>0006-497</u></a>	Dispersive (rectangular) aperture Precision Demountable Cell, without windows	<b>\$195.50</b>
<a href="#"><u>0006-604</u></a>	FTIR (circular) aperture Precision Demountable Cell, without windows	<b>\$195.00</b>
<a href="#"><u>0006-4152</u></a>	Adapter Ring to convert Precision Demountable Cell for use with 25mm windows	<b>\$63.00</b>
<a href="#"><u>0006-6902</u></a>	Thumbscrews for Precision Demountable Cell, pk/4	<b>\$94.00</b>
<a href="#"><u>0006-5064</u></a>	Thumbscrews for Precision Demountable Cell with 2mm thick windows, pk/4	<b>\$92.00</b>
<a href="#"><u>0006-9530</u></a>	Delrin Optical Alignment Cavity	<b>\$73.00</b>

**The Precision Demountable Cell is ideal for mulls, capillary films, cast films and thin films of finely powdered solids in slurry form**

### INTERNATIONAL CRYSTAL LABORATORIES

11 Erie Street, Garfield, NJ. 07026

[www.internationalcrystal.net](http://www.internationalcrystal.net)

[icmail@internationalcrystal.net](mailto:icmail@internationalcrystal.net)

Phone: 973-478-8944.

